## AQ1280

The AQ1280 appliance uses
Prolitec's patented technology
to diffuse fragrance and odor
treatment products into the air.
This appliance was designed
for professional use, in direct
diffusion or through an HVAC
system.



50 intensity levels and timing options give you control.

Perfectly scents spaces up to 150,000 cubic feet.

Tiny droplets convert to vapor within milliseconds.







## AQ1280

Technical Specifications	Туре	Single nebulizer head
	Cartridge	1250mL or 2500mL recyclable
	Droplet size	About one micron
Power Specifications	Input	100 – 240 VAC, 0.4A Max, 50/60 Hz
	Protection	Class 2 power supply
	Internal	Real time clock with permanent backup battery
	Output	15VDC at 1.2A
Performance & Settings	Coverage	Up to 150,000 ft <sup>3</sup> (4,250 m <sup>3</sup> )
	Programs	Up to 21 start/stop times per day 24/7 mode
	Settings	50 intensity levels
	Off-cycle	30 seconds, 2 minutes or 7 minutes
	Enclosure	Grey fiberglass with swinging door, NEMA 4 rated
	Safety Approval	CB, CE, & FCC Part 15, ROHS compliant
	Environment	0° to 40° C, <85% Humidity
Dimensions & Installation	Size	15½" x 13½" x 6¾" (39.4cm x 34cm x 17.2cm)
	Weight	13.7 lbs. (6.2kg) with 1250mL cartridge 15.4 lbs. (7.0kg) with 2500mL cartridge
	Mounting	Wall mount, with and without fan  HVAC mount  Tabletop/floor mount, with feet

## PROLITEC. PERFECTLY SCENTED ENVIRONMENTS

PROLITEC sets the standard for enhancing indoor environments through fragrance.

Prolitec Inc. | 1235 W. Canal Street | Milwaukee, WI 53233